
	Wenzhou Delikang Electronic Co.,Ltd	
	ADD:No.3 Sanxi road(building 2),south of quxi industry area,Wenzhou city ,Zhejiang,China	
	TEL: (86)579-86-135-333 FAX: (86)577-86-132-238	
	Model :DLK-B005	

Product Picture	Details of the product	
	Model No.	DLK-B005
	Product name	Coin -operated massage chair
	Type of coin box	memory machine of single currency 1coin type memory machine of multiple currency 3coins type
	Dimension	Massage chair 115*79*76CM
	Pcs/Carton	1PC/2CTN
	G.W./N.W.	88KGS /75KGS
	M.O.Q.	10SETS
	1*20'FT Container	36SETS
	1*40'GP Container	78SETS
	Material	High qulaity PU or Real leather

Certificate : CE ROHS

Product Description
<p>1.Coin machine is installed in armrest</p> <p>2.Digital display shows the remaining working time.</p> <p>3.It is availbale for both home and pubic use,the remote controller will be regarded as invalid without inserting money under pubilc mode,or you need to start as a home machine through an exclusive connector.</p> <p>4.Auto reclining and massage under public mode,it helps users in more comfortable condition for massage.</p> <p>5..Equipped with a mechanism of muted massage rollers which is able to move up and down at back.</p> <p>6.Auto and manual in optional mode ,user can select favourite massage program through remote controller</p> <p>7.Four massage tech are available for back massage:knead,shiatsu,knock and sychronous knead &knock</p> <p>8.Three different speed and different shoulder width are available.</p> <p>9.12pcs of airbags are set at seat and leg rest and three intensity are availbale.</p> <p>10.Three different time program in optional selection</p> <p>11..Linkage or individual operation are available for regulating the reclining of legrest and back rest</p> <p>12.Auto rest function:All of massage rollers,back rest and leg rest will be reset if the machine is offe</p> <p>13.Equipped with the swivel wheels which can be flexible to move the machine.</p> <p>Fabric Material: high quality PU</p>

The Specification of Product

Product Name	Music Massage Chair
Model	DLK-B005
Nominal Voltage	<input type="checkbox"/> AC100-120V <input type="checkbox"/> AC220-240V
Rated Power	180W
Rated Frequency	50HZ-60HZ
Rated Operation Time	15 Minutes

Note:

Apply to coin's diameter=18m/m 29m/m

Apply to coin's thickness=1.2m/m 3.0m/m

Work voltage=DC 12V±20%

Temperature= -20°to 50°

Adjust the kinds of coins:RMB.HK dollar,Australian dollar,US dollar,Euro dollar,Canadian dollar,Pound ,Tai dollar,etc

Box color: offwhite or Black (optional)